

E5BB1160



Collection: MICROMÉGA DUO

Finish*:



00 - White

Main features:



Features

- **DIMENSIONS:** 150 x 100 cm
- **MATERIAL:** Acrylic
- **VOLUME:** 125
- **MASSAGES TYPE:** Silence and Tonic: 2 invigorating massage programmes to choose from
- **WHIRLPOOL BATH TYPE:** Corner baths
- 1 high-luminosity LED spotlight
- Pump (900 W)

- **WEIGHT:** 52 kg
- **INSTALLATION TYPE:** Drop-in
- **MASSAGES:** Water massage
- **JETS:** 6 rotating side jets, 4 back mini-jets, 2 foot mini-jets: Flush fit for a discrete, clean look
- **VERSION:** Right
- 1 self-supporting frame for easier installation
- Waterfall headrest for targeted neck action: (add "-M" prefix to finish code "-00")

Consumer benefits

- **MORE COMFORTABLE AND ESTHETIC:** Invisible injectors at the bottom of the bath.
- **QUIET:** Quiet blower reduces noise on whirlpool baths, an Acoustics kit (standard or optional, depending on the system) and optional Silence Box enhance soundproofing.
- **EASY CLEANING:** Automatic ozone sanitising after each bath and a cleaning program included on Energy+ and Serenity+ whirlpools.
- **SAFETY:** Water-level sensor prevents system from operating if water level is not high enough.
- **MADE IN FRANCE :** Our whirlpool baths are manufactured in our plant in Troyes


Installation benefits

- **EASY INSTALLATION:** Thanks to the self-supporting frame

Required products

- E6D015: Extra-slim waste with overflow
- E70174: Pop-up waste

Technical drawing



Product Specification: Plus system, bath 150 cm. E5BB1160. Collection: MICROMÉGA DUO. DIMENSIONS: 150 x 100 cm. WEIGHT: 52 kg. MATERIAL: Acrylic. INSTALLATION TYPE: Drop-in. VOLUME: 125. MASSAGES: Water massage. MASSAGES TYPE: Silence and Tonic: 2 invigorating massage programmes to choose from. JETS: 6 rotating side jets, 4 back mini-jets, 2 foot mini-jets: Flush fit for a discrete, clean look. WHIRLPOOL BATH TYPE: Corner baths. VERSION: Right. 1 high-luminosity LED spotlight. 1 self-supporting frame for easier installation. Pump (900 W). Waterfall headrest for targeted neck action: (add "-M" prefix to finish code "-00").

*Due to possible variations in computer and printer calibrations, technical factors and certain finish characteristics, the colors you see may not accurately portray the actual colors and are provided as a guide only.